

Slash Resistant Synthetic Glove

Police Patrol Glove, Style No: SB02793A

CONSTRUCTION

These synthetic gloves offer a winning combination of protection, dexterity and second skin comfort. The outer palm is made from clarino synthetic leather that is highly breathable with good grip characteristics. Lined with ARMORTEX cut resistant fabric on the palm providing the very highest level of cut protection, the glove is cut on an ergonomic pattern that mimics the natural hand shape making it comfortable to wear for long periods. A rubberised adjustable velcro strap ensures a firm closure around the wrist and touch screen active material on the tip of the index finger and thumb allows users to work their portable devices while the gloves stay on their hands keeping users protected for longer. Stretch fabric with neoprene knuckles across the back of the hand ensures a close, breathable and but comfortable fit.

PURPOSE

It is designed to offer the wearer a high degree of dexterity and protection during routine operations and training exercises.

FABRIC SPECIFICATIONS

Clarino™ breathable synthetic leather palm

Lined with Armor-tex cut resistant aramid fabric Neoprene knuckles to offer maximum comfort and flexibility

Breathable TrekDry keeps hands cool and comfortable

4 way stretch elastane fabric on back of hand

Elasticated cuff with TPR closure, for maximum adjustability.

SIZES

XXS/6, XS/7, S/8, M/9, L/10, XL/11, XXL/12, XXXL/13

+ Bespoke upon request



- Full synthetic exterior with reinforced palm and thumb
- Lined with ARMORTEX to provide best possible levels of cut protection
- Close anatomical fit for second skin comfort
- Adjustable strap for secure fit to wrist
- Touch screen active thumb and index finger tip
- Tested to EN420:2003 + A1:2009 and EN388:2016

Slash Resistant Synthetic Glove

Police Taser Glove, Style No: SB02793A

TEST RESULTS

| PROPERTY | LEVEL | METHOD | PROPERTY | LEVEL | METHOD |
|----------------------|-------|------------|---------------------|-------|------------|
| Abrasion Resistance | 2 | EN388:2016 | Tear Resistance | 4 | EN388:2016 |
| Blade/Cut Resistance | 5 | EN388:2016 | Puncture Resistance | 2 | EN388:2016 |

GLOVE CARE AND MAINTENANCE

Gloves that are deemed non-repairable are to be disposed of when damaged. Gloves do not require the use of specialist solvent-based products for cleaning or maintenance and these should not be used under any circumstances. The design and materials used ensure that the user can maintain the gloves in hygienic condition. For best results follow this procedure:

- Sponge clean
- Hang to dry away from direct sunlight or heat
- Clean gloves before they become too soiled.
- A sponge not a stiff brush is recommended to be used for ingrained grime.



Southcombe Brothers Ltd
Stoke-sub-Hamdon
Somerset TA14 6QD
UK

Phone: +44 (0) 1935 823567
Fax: +44 (0) 1935 822918
E-mail: sales@southcombe.com
www.southcombe.com